

A	Skin	Size
	40.5" (1028.7 <sub>mm</sub> ) X 40.5" (1028.7 <sub>mm</sub> )	W
		H
Diamond		Diamond Shown as it will appear on the Xpressions unit

B	Skin	Size
	40.5" (1028.7 <sub>mm</sub> ) X 40.5" (1028.7 <sub>mm</sub> )	W
		H
Diamond		Diamond Shown as it will appear on the Xpressions unit


C	Skin	Size
	29.5" (749.3 <sub>mm</sub> ) X 29.5" (749.3 <sub>mm</sub> )	W
		H
1x1 Single Twist		1x1 Single Twist Shown as it will appear on the Xpressions unit

D	Skin	Size
	29.5" (749.3 <sub>mm</sub> ) X 29.5" (749.3 <sub>mm</sub> )	W
		H
1x1 Single Twist		1x1 Single Twist Shown as it will appear on the Xpressions unit

E	Skin	Size
	29.5" (749.3 <sub>mm</sub> ) X 29.5" (749.3 <sub>mm</sub> )	W
		H
1x1 Single Twist		1x1 Single Twist Shown as it will appear on the Xpressions unit

F	Skin	Size
	29.5" (749.3 <sub>mm</sub> ) X 29.5" (749.3 <sub>mm</sub> )	W
		H
1x1 Single Twist		1x1 Single Twist Shown as it will appear on the Xpressions unit

It is recommended that all text and borders be 2" from the finish size



### Focus Area Key

focus area is always 3"-5" inside edge of all four sides on all skin styles and sizes